SIEMENS

Data sheet

6AG1511-1AL03-7AB0



SIPLUS S7-1500 CPU 1511-1 PN based on 6ES7511-1AL03-0AB0 with conformal coating -40...+70 $^{\circ}\text{C}$. central processing unit with work memory 300 KB for program and 1.5 MB for data, 1st interface: PROFINET IRT with 2-port switch, 25 ns bit performance, SIMATIC Memory Card required

Figure similar

5 · · · · · · · · · · · · · · · · · · ·	
General information	
Product type designation	CPU 1511-1 PN
Firmware version	
FW update possible	Yes
based on	6ES7511-1AL03-0AB0
Product function	
● I&M data	Yes; I&M0 to I&M3
Isochronous mode	Yes; Distributed and central; with minimum OB $6x$ cycle of $500~\mu s$ (distributed) and 1 ms (central)
Engineering with	
STEP 7 TIA Portal configurable/integrated from version	see entry ID: 109746275
Configuration control	
via dataset	Yes
Display	
Screen diagonal [cm]	3.45 cm
Control elements	
Number of keys	8
Mode buttons	2
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Mains buffering	
 Mains/voltage failure stored energy time 	5 ms
Repeat rate, min.	1/s
Input current	
Current consumption (rated value)	0.73 A
Current consumption, max.	0.9 A
Inrush current, max.	1.15 A; Rated value
l²t	0.5 A ² ·s
Power	
Infeed power to the backplane bus	10 W
Power consumption from the backplane bus (balanced)	5.5 W
Power loss	
Power loss, typ.	7.5 W
Memory	
Number of slots for SIMATIC memory card	1
SIMATIC memory card required	Yes

Work memory	
integrated (for program)	300 kbyte
integrated (for data)	1.5 Mbyte
Load memory	
Plug-in (SIMATIC Memory Card), max.	32 Gbyte
Backup	
maintenance-free	Yes
CPU processing times	
for bit operations, typ.	25 ns
for word operations, typ.	32 ns
for fixed point arithmetic, typ.	42 ns
for floating point arithmetic, typ.	170 ns
CPU-blocks	
Number of elements (total)	4 000; Blocks (OB, FB, FC, DB) and UDTs
DB	
Number range	1 60 999; subdivided into: number range that can be used by the user: 1
•	59 999, and number range of DBs created via SFC 86: 60 000 60 999
• Size, max.	1.5 Mbyte; For DBs with absolute addressing, the max. size is 64 KB
FB	
Number range	0 65 535
• Size, max.	300 kbyte
FC	
Number range	0 65 535
• Size, max.	300 kbyte
OB	
• Size, max.	300 kbyte
Number of free cycle OBs	100
Number of time alarm OBs	20
Number of delay alarm OBs	20
Number of cyclic interrupt OBs	20; With minimum OB 3x cycle of 250 µs
Number of process alarm OBs	50
Number of DPV1 alarm OBs	3
Number of isochronous mode OBs	2
Number of technology synchronous alarm OBs	2
Number of startup OBs	100
Number of startup OBs Number of asynchronous error OBs	4
Number of synchronous error OBs	2
Number of diagnostic alarm OBs	1
Nesting depth	0.4
per priority class	24
Counters, timers and their retentivity	
S7 counter	
Number	2 048
Retentivity	
— adjustable	Yes
IEC counter	
Number	Any (only limited by the main memory)
Retentivity	
— adjustable	Yes
S7 times	
Number	2 048
Retentivity	
— adjustable	Yes
IEC timer	
Number	Any (only limited by the main memory)
Retentivity	
— adjustable	Yes
Data areas and their retentivity	
Retentive data area (incl. timers, counters, flags), max.	256 kbyte; in total; available retentive memory for bit memories, timers,
, , ,	counters, DBs, and technology data (axes): 216 KB
Extended retentive data area (incl. timers, counters, flags), max.	1.5 Mbyte; When using PS 6 0W 24/48/60 V DC HF

Flag	
• Size, max.	16 kbyte
Number of clock memories	8; 8 clock memory bit, grouped into one clock memory byte
Data blocks	e, a diadk mamary bit, grouped mile and diadk mamary byte
Retentivity adjustable	Yes
Retentivity preset	No
Local data	
per priority class, max.	64 kbyte; max. 16 KB per block
Address area	a conjugation of the part action
Number of IO modules	2 048; max. number of modules / submodules
I/O address area	
• Inputs	32 kbyte; All inputs are in the process image
Outputs	32 kbyte; All outputs are in the process image
per integrated IO subsystem	
— Inputs (volume)	8 kbyte
— Outputs (volume)	8 kbyte
per CM/CP	
— Inputs (volume)	8 kbyte
— Outputs (volume)	8 kbyte
Subprocess images	
Number of subprocess images, max.	32
Hardware configuration	
Number of distributed IO systems	32; A distributed I/O system is characterized not only by the integration of distributed I/O via PROFINET or PROFIBUS communication modules, but also by the connection of I/O via AS-i master modules or links (e.g. IE/PB-Link)
Number of DP masters	
	4; A maximum of 4 CMs/CPs (PROFIBUS, PROFINET, Ethernet) can be inserted in total
Number of IO Controllers	
• integrated	1
• Via CM	4; A maximum of 4 CMs/CPs (PROFIBUS, PROFINET, Ethernet) can be inserted in total
Rack	
 Modules per rack, max. 	32; CPU + 31 modules
Number of lines, max.	1
PtP CM	
Number of PtP CMs	the number of connectable PtP CMs is only limited by the number of available slots
Time of day	
Clock	
• Type	Hardware clock
Backup time	6 wk; At 40 °C ambient temperature, typically
Deviation per day, max.	10 s; Typ.: 2 s
Operating hours counter	
• Number	16
Clock synchronization	V
• supported	Yes
• in AS, master	Yes
• in AS, device	Yes
on Ethernet via NTP Interfaces	Yes
Interfaces	4
Number of PROFINET interfaces	1
1. Interface	
Interface types	Voc. V1
RJ 45 (Ethernet) Number of parts	Yes; X1
Number of ports integrated switch	2 Voc
• integrated switch	Yes
Protocols • IP protocol	Yes; IPv4
PROFINET IO Controller	Yes
PROFINET IO Controller PROFINET IO Device	Yes
SIMATIC communication	Yes
	100

Yes; Optionally also encrypted • Open IE communication Web server Yes Media redundancy Yes **PROFINET IO Controller** Services - PG/OP communication Yes Yes Isochronous mode - Direct data exchange Yes; Requirement: IRT and isochronous mode (MRPD optional) — IRT - PROFlenergy Yes; per user program Yes; Max. 32 PROFINET devices Prioritized startup 128; In total, up to 512 distributed I/O devices can be connected via AS-i, PROFIBUS or PROFINET $\,$ - Number of connectable IO Devices, max. - Of which IO devices with IRT, max. 64 - Number of connectable IO Devices for RT, max. 128 128 - of which in line, max. - Number of IO Devices that can be simultaneously 8; in total across all interfaces activated/deactivated, max. Number of IO Devices per tool, max. 8 - Updating times The minimum value of the update time also depends on communication share set for PROFINET IO, on the number of IO devices, and on the quantity of configured user data Update time for IRT — for send cycle of 250 µs $250~\mu s$ to 4 ms; Note: In the case of IRT with isochronous mode, the minimum update time of 500 µs of the isochronous OB is decisive 500 µs to 8 ms; Note: In the case of IRT with isochronous mode, the minimum — for send cycle of 500 µs update time of 625 µs of the isochronous OB is decisive - for send cycle of 1 ms 1 ms to 16 ms - for send cycle of 2 ms 2 ms to 32 ms - for send cycle of 4 ms 4 ms to 64 ms - With IRT and parameterization of "odd" send cycles Update time = set "odd" send clock (any multiple of 125 μ s: 375 μ s, 625 μ s ... 3 875 µs) Update time for RT 250 µs to 128 ms — for send cycle of 250 µs — for send cycle of 500 µs 500 µs to 256 ms - for send cycle of 1 ms 1 ms to 512 ms - for send cycle of 2 ms 2 ms to 512 ms - for send cycle of 4 ms 4 ms to 512 ms **PROFINET IO Device** Services - PG/OP communication Yes No - Isochronous mode - IRT Yes - PROFlenergy Yes; per user program Shared device Yes - Number of IO Controllers with shared device, max. activation/deactivation of I-devices Yes; per user program - Asset management record Yes; per user program Interface types RJ 45 (Ethernet) • 100 Mbps Yes Autonegotiation Yes Autocrossing Yes • Industrial Ethernet status LED Yes **Protocols PROFIsafe** No Number of connections • Number of connections, max. 128; via integrated interfaces of the CPU and connected CPs / CMs • Number of connections reserved for ES/HMI/web 10 • Number of connections via integrated interfaces 88 • Number of S7 routing paths 16 Redundancy mode • H-Sync forwarding Yes

Media redundancy	1 . 4
— Media redundancy	only via 1st interface (X1)
— MRP	Yes; MRP Automanager according to IEC 62439-2 Edition 2.0, MRP Manager; MRP Client
 MRP interconnection, supported 	Yes; as MRP ring node according to IEC 62439-2 Edition 3.0
— MRPD	Yes; Requirement: IRT
 Switchover time on line break, typ. 	200 ms; For MRP, bumpless for MRPD
 Number of stations in the ring, max. 	50
SIMATIC communication	
 PG/OP communication 	Yes; encryption with TLS V1.3 pre-selected
• S7 routing	Yes
Data record routing	Yes
 S7 communication, as server 	Yes
 S7 communication, as client 	Yes
User data per job, max.	See online help (S7 communication, user data size)
Open IE communication	
• TCP/IP	Yes
— Data length, max.	64 kbyte
 several passive connections per port, supported 	Yes
• ISO-on-TCP (RFC1006)	Yes
— Data length, max.	64 kbyte
• UDP	Yes
— Data length, max.	2 kbyte; 1 472 bytes for UDP broadcast
— UDP multicast	Yes; max. 78 multicast circuits
• DHCP	Yes
• DNS	Yes
• SNMP	Yes
• DCP	Yes
• LLDP	Yes
Encryption	Yes; Optional
Web server	
• HTTP	Yes; Standard and user pages
• HTTPS	Yes; Standard and user pages
OPC UA	
 Runtime license required 	Yes; "Small" license required
OPC UA Client	Yes; Data Access (registered Read/Write), Method Call
 Application authentication 	Yes
— Security policies	Available security policies: None, Basic128Rsa15, Basic256Rsa15, Basic256Sha256
— User authentication	"anonymous" or by user name & password
 Number of connections, max. 	4
	7
 Number of nodes of the client interfaces, recommended max. 	1 000
	1 000
recommended max. — Number of elements for one call of OPC_UA_NodeGetHandleList/OPC_UA_ReadList/OPC_I	1 000
recommended max. — Number of elements for one call of OPC_UA_NodeGetHandleList/OPC_UA_ReadList/OPC_U max. — Number of elements for one call of	1 000
recommended max. — Number of elements for one call of OPC_UA_NodeGetHandleList/OPC_UA_ReadList/OPC_I max. — Number of elements for one call of OPC_UA_NameSpaceGetIndexList, max. — Number of elements for one call of	1 000 300 20
recommended max. — Number of elements for one call of OPC_UA_NodeGetHandleList/OPC_UA_ReadList/OPC_U max. — Number of elements for one call of OPC_UA_NameSpaceGetIndexList, max. — Number of elements for one call of OPC_UA_MethodGetHandleList, max. — Number of simultaneous calls of the client instructions for session management, per connection,	1 000 300 20 100
recommended max. — Number of elements for one call of OPC_UA_NodeGetHandleList/OPC_UA_ReadList/OPC_U max. — Number of elements for one call of OPC_UA_NameSpaceGetIndexList, max. — Number of elements for one call of OPC_UA_MethodGetHandleList, max. — Number of simultaneous calls of the client instructions for session management, per connection, max.	1 000 300 20 100
recommended max. — Number of elements for one call of OPC_UA_NodeGetHandleList/OPC_UA_ReadList/OPC_U max. — Number of elements for one call of OPC_UA_NameSpaceGetIndexList, max. — Number of elements for one call of OPC_UA_MethodGetHandleList, max. — Number of simultaneous calls of the client instructions for session management, per connection, max. — Number of simultaneous calls of the client	1 000 300 20 100
recommended max. — Number of elements for one call of OPC_UA_NodeGetHandleList/OPC_UA_ReadList/OPC_I max. — Number of elements for one call of OPC_UA_NameSpaceGetIndexList, max. — Number of elements for one call of OPC_UA_MethodGetHandleList, max. — Number of simultaneous calls of the client instructions for session management, per connection, max. — Number of simultaneous calls of the client instructions for data access, per connection, max.	1 000 300 20 100 1
recommended max. — Number of elements for one call of OPC_UA_NodeGetHandleList/OPC_UA_ReadList/OPC_I max. — Number of elements for one call of OPC_UA_NameSpaceGetIndexList, max. — Number of elements for one call of OPC_UA_MethodGetHandleList, max. — Number of simultaneous calls of the client instructions for session management, per connection, max. — Number of simultaneous calls of the client instructions for data access, per connection, max. — Number of registerable nodes, max. — Number of registerable method calls of	1 000 300 20 100 1 5 5 000
recommended max. — Number of elements for one call of OPC_UA_NodeGetHandleList/OPC_UA_ReadList/OPC_I max. — Number of elements for one call of OPC_UA_NameSpaceGetIndexList, max. — Number of elements for one call of OPC_UA_MethodGetHandleList, max. — Number of simultaneous calls of the client instructions for session management, per connection, max. — Number of simultaneous calls of the client instructions for data access, per connection, max. — Number of registerable nodes, max. — Number of registerable method calls of OPC_UA_MethodCall, max. — Number of inputs/outputs when calling	1 000 300 20 100 1 5 5 000 100
recommended max. — Number of elements for one call of OPC_UA_NodeGetHandleList/OPC_UA_ReadList/OPC_L max. — Number of elements for one call of OPC_UA_NameSpaceGetIndexList, max. — Number of elements for one call of OPC_UA_MethodGetHandleList, max. — Number of simultaneous calls of the client instructions for session management, per connection, max. — Number of simultaneous calls of the client instructions for data access, per connection, max. — Number of registerable nodes, max. — Number of registerable method calls of OPC_UA_MethodCall, max. — Number of inputs/outputs when calling OPC_UA_MethodCall, max.	1 000 300 20 100 1 5 5 000 100 20 Yes; Data Access (Read, Write, Subscribe), Method Call, Alarms & Condition

— User authentication	"anonymous" or by user name 9 necessary
— Oser authernication — GDS support (certificate management)	"anonymous" or by user name & password Yes
Number of sessions, max.	32
	50 000
Number of accessible variables, max.	10 000
Number of registerable nodes, max.	
Number of subscriptions per session, max.	50
— Sampling interval, min.	100 ms
— Publishing interval, min.	200 ms
Number of server methods, max.	20
Number of inputs/outputs per server method, max.	20
Number of monitored items, recommended max.	4 000; for 1 s sampling interval and 1 s send interval
Number of server interfaces, max.	10 of each "Server interfaces" / "Companion specification" type and 20 of the type "Reference namespace"
 Number of nodes for user-defined server interfaces, max. 	15 000
 Alarms and Conditions 	Yes
 Number of program alarms 	100
Number of alarms for system diagnostics	50
Further protocols	
• MODBUS	Yes; MODBUS TCP
S7 message functions	
Number of login stations for message functions, max.	32
Program alarms	Yes
Number of configurable program messages, max.	5 000; Program messages are generated by the "Program_Alarm" block, ProDiag or GRAPH
Number of loadable program messages in RUN, max.	2 500
Number of simultaneously active program alarms	
 Number of program alarms 	600
 Number of alarms for system diagnostics 	100
 Number of alarms for motion technology objects 	160
Test commissioning functions	
Joint commission (Team Engineering)	Yes; Parallel online access possible for up to 5 engineering systems
Status block	Yes; Up to 8 simultaneously (in total across all ES clients)
Single step	No
Number of breakpoints	8
Status/control	
Status/control variable	Yes
 Variables 	Inputs/outputs, memory bits, DBs, distributed I/Os, timers, counters
 Number of variables, max. 	
— of which status variables, max.	200; per job
— of which control variables, max.	200; per job
Forcing	
• Forcing	Yes
Forcing, variables	Peripheral inputs/outputs
Number of variables, max.	200
Diagnostic buffer	
• present	Yes
Number of entries, max.	1 000
— of which powerfail-proof	500
Traces	
Number of configurable Traces	4; Up to 512 KB of data per trace are possible
Interrupts/diagnostics/status information	, , ,
Diagnostics indication LED	
RUN/STOP LED	Yes
• ERROR LED	Yes
MAINT LED	Yes
STOP ACTIVE LED Connection display LINK TY/DY	Yes
Connection display LINK TX/RX	Yes
Supported technology objects	V All The least the second sec
Motion Control	Yes; Note: The number of technology objects affects the cycle time of the PLC program; selection guide via the TIA Selection Tool
 Number of available Motion Control resources for 	1 120

technology objects	
 Required Motion Control resources 	
 per speed-controlled axis 	40
per positioning axis	80
per synchronous axis	160
— per external encoder	80
— per output cam	20
— per cam track	160
— per probe	40
Positioning axis	
Number of positioning axes at motion control cycle of 4 ms (typical value)	11
Number of positioning axes at motion control cycle of 8 ms (typical value)	14
Controller	
PID_Compact	Yes; Universal PID controller with integrated optimization
PID_3Step	Yes; PID controller with integrated optimization for valves
• PID-Temp	Yes; PID controller with integrated optimization for temperature
Counting and measuring	. 55, 5 controller man integrated optimization for temperature
High-speed counter	Yes
	l Co
Ambient conditions	
Ambient temperature during operation	
horizontal installation, min.	-40 °C; = Tmin (incl. condensation/frost)
horizontal installation, max.	70 °C; = Tmax; display: 50 °C, the display is switched off at an operating temperature of typically 50 °C
 vertical installation, min. 	-40 °C; = Tmin
 vertical installation, max. 	40 °C; = Tmax; display: 40 °C, at an operating temperature of typically 40 °C,
Ambient temperature during storage/transportation	the display is switched off
Ambient temperature during storage/transportation	40.00
• min.	-40 °C
• max.	70 °C
Altitude during operation relating to sea level	
Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual
Relative humidity	
 With condensation, tested in accordance with IEC 60068- 2-38, max. 	100 %; RH incl. condensation / frost (no commissioning in bedewed state), horizontal installation
Resistance	
Coolants and lubricants	
 Resistant to commercially available coolants and lubricants 	Yes; Incl. diesel and oil droplets in the air
Use in stationary industrial systems	
 to biologically active substances according to EN 60721-3-3 	Yes; Class 3B2 mold, fungus and dry rot spores (with the exception of fauna); Class 3B3 on request
 to chemically active substances according to EN 60721-3-3 	Yes; Class 3C4 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *
 to mechanically active substances according to EN 60721-3-3 	Yes; Class 3S4 incl. sand, dust, *
Use on ships/at sea	
 to biologically active substances according to EN 60721-3-6 	Yes; Class 6B2 mold, fungal and dry rot spores (excluding fauna)
 to chemically active substances according to EN 60721-3-6 	Yes; Class 6C3 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *
 to mechanically active substances according to EN 60721-3-6 	Yes; Class 6S3 incl. sand, dust; *
Usage in industrial process technology	
Against chemically active substances acc. to EN 60654-4	Yes; Class 3 (excluding trichlorethylene)
 Environmental conditions for process, measuring and control systems acc. to ANSI/ISA-71.04 	Yes; Level GX group A/B (excluding trichlorethylene; harmful gas concentrations up to the limits of EN 60721-3-3 class 3C4 permissible); level LC3 (salt spray) and level LB3 (oil)
Remark	(
Note regarding classification of environmental conditions acc. to EN 60721, EN 60654-4 and ANSI/ISA-71.04	* The supplied plug covers must remain in place over the unused interfaces during operation!
Conformal coating	
9	Vec: Class 2 for high reliability
Coatings for printed circuit board assemblies acc. to EN	Yes; Class 2 for high reliability

61086

• Protection against fouling acc. to EN 60664-3

• Military testing according to MIL-I-46058C, Amendment 7

 Qualification and Performance of Electrical Insulating Compound for Printed Board Assemblies according to IPC-CC-830A Yes; Type 1 protection

Yes; Discoloration of coating possible during service life

Yes; Conformal coating, Class A

configuration / header	
configuration / programming / header	
Programming language	
— LAD	Yes
— FBD	Yes
— STL	Yes
— SCL	Yes
— GRAPH	Yes
Know-how protection	
 User program protection/password protection 	Yes
 Copy protection 	Yes
Block protection	Yes
Access protection	
 protection of confidential configuration data 	Yes
 Password for display 	Yes
 Protection level: Write protection 	Yes
 Protection level: Read/write protection 	Yes
 Protection level: Complete protection 	Yes
programming / cycle time monitoring / header	
 lower limit 	adjustable minimum cycle time
• upper limit	adjustable maximum cycle time
Dimensions	
Width	35 mm
Height	147 mm
Depth	129 mm
Weights	
Weight, approx.	400 g

last modified:

